

Technical Whitepaper

Chip Sleeve / Chip Can Insert · 180° half-cylinder · 5.5 oz stacked-chip canister · DOC-CS-100 Rev F · Inventor: Deanna Fine

1. Summary

The Chip Sleeve is a rigid, single-piece insert that occupies one half of the cross-section of a standard stacked-chip canister. It is a true 180° half-cylinder with a closed lower end, an open upper end, and a full-height open side, so the chip column bears on both sides of the curved wall. The consumer tilts the can and withdraws the sleeve; the stack rides out intact and sits supported on the sleeve. Nothing about the exterior of the canister changes.

2. Problem

Stacked-chip canisters are deeper than the average adult hand can comfortably reach. Consumers tip the can, shake it, or force a hand down the tube — all of which fracture chips, and the last third of the pack is routinely eaten as fragments or discarded. It is a well-known, universally recognised failure point of an otherwise excellent package.

3. Geometry

Derived from the 5.5 oz canister interior. The curved wall is swept through exactly 180°, giving a half-moon cross-section rather than a wrapping cradle. This is the geometry described in the provisional filing. Rev F length is set from a direct measurement of the canister interior (≈ 9 in / 228.6 mm floor to under-lip), not from a published exterior height.

Parameter	Nominal	Tolerance
Canister outside diameter	76.1 mm	± 0.5
Canister wall thickness	1.2 mm	± 0.2
Canister inside diameter	73.7 mm	± 0.4
Canister usable interior depth (measured)	228.6 mm (9.00 in)	± 2.0
Sleeve curved-wall O.D.	72.9 mm	± 0.15
Overall sleeve length	220.0 mm (8.66 in)	+0 / -1.0
Radial sliding clearance per side	0.40 mm	0.32 - 0.48
Diametral sliding clearance	0.80 mm	0.64 - 0.96
Wall thickness — PP	0.25 mm	± 0.05
Wall thickness — paperboard	0.40 mm	± 0.08
Arc of curved wall	180°	—

The 0.40 mm per-side radial clearance is a running fit: loose enough to slide freely under light finger load with product in place, tight enough that the sleeve cannot rack or bind inside the tube during withdrawal. The 220.0 mm length leaves roughly 8.6 mm of clearance beneath the canister lip so the lid reseats normally with the sleeve in place.

4. Materials

The part is material-agnostic, and food-grade in every production route. Two are under evaluation:

— Food-grade polypropylene (PP, PET or rPET) at 0.25 mm wall — thermoformed or injection moulded. Target part mass ~6 g. Highest stiffness-to-mass, best surface finish, tolerant of oil and low humidity.

— Barrier-coated paperboard (SBS or CRB) at 0.40 mm — die-cut, scored and form-wrapped on a mandrel. Target part mass ~5 g. Recycles with the existing composite tube, which is the preferred outcome for most fibre-forward packaging roadmaps.

Both routes require food-contact-compliant material and certification by the licensee (FDA 21 CFR / EU 10-2011 as applicable). Paperboard additionally requires a food-safe grease and moisture barrier (PE, PLA or a water-based coating) to prevent oil migration and paper dust. Rigidity is achieved through wall thickness and, if required, a rolled lip along the two straight edges of the half-cylinder.

Note: 3D-printed samples are for fit and form validation only — common SLA resins are not food-safe and must not be used for chip contact. Mass figures are the inventor's stated targets and are subject to validation by the licensee's engineering and packaging teams.

5. Structural behaviour

Under withdrawal the sleeve is loaded as a cantilevered open channel. The 180° section has a high second moment of area about the horizontal axis, which is the axis that matters: the load is the weight of the chip column (typically 150–160 g) applied along the trough. The closed lower end acts as a stop that prevents the stack from sliding off the far end during withdrawal. At the Rev F 0.25 mm production wall, stiffness must be confirmed by the licensee on the chosen substrate; prototype prints are supplied at 0.50 mm to survive handling.

6. Line integration concept

Stacked-chip canisters are charged through the open base: chips are formed into a continuous column, counted, and pushed into the tube as a single slug before the metal base is seamed on. The proposed Chip Sleeve integration is a co-insertion concept — a magazine at the transfer chute would present a sleeve, the counted column would be lowered vertically into the open trough (never pushed through the closed end), and sleeve plus stack would enter the can as one slug in the existing push stroke.

This is an engineering hypothesis, not a validated production configuration. Added modules, station count, cycle time, and any line-speed impact can only be confirmed through a study with the OEM's line engineer. The goal is one bolt-on module, no second station, and no line-speed penalty.

7. Cost model

Figures are order-of-magnitude estimates for planning only, at volumes typical of a single regional SKU. Final costs depend on validated part mass, material choice, and the OEM's process.

CHIP SLEEVE / CHIP CAN INSERT

DOC-CS-100 Rev F · Provisional patent filed · Non-confidential

Item	PP 0.25 mm	Paperboard 0.40 mm
Resin / board per part	\$0.008	\$0.005
Conversion per part	\$0.008	\$0.007
Estimated landed cost	\$0.016	\$0.012
Tooling (per cavity family)	\$45k - \$80k	\$20k - \$35k
Target added part mass	~6 g	~5 g
Incremental freight cost	\$0.00 (no added cube)	\$0.00 (no added cube)

8. Intellectual property

A provisional patent application has been filed covering the half-cylinder insert geometry — closed lower end, open upper end, full-height open side — and the tilt-and-withdraw method of dispensing a stacked column from a canister. Available for licence on a category or geographic exclusivity basis, per-unit royalty, or outright assignment.

Appendix A — Dimensioned drawing

DWG-CS-001 Rev F. Scaled variants exist for 75 mm and 83 mm canister formats; all retain the 180° arc and the 0.40 mm per-side clearance rule.

Revision history

Rev	Change
D	Contact details corrected; construction and integration notes clarified.
E	Wall reduced to 0.25 mm; length shortened after prototype fit failure.
F	Length set to 220.0 mm from measured canister interior depth (9 in). Mass, cost, and food-grade material notes updated to match.